


HEATSINK
REQUIRED


PHOTOCELL
10k-5M, PDV-P9203
OPEN=IR ON
LOW R=IR OFF
TELEMETRY
EXT. ON/OFF
SHORT= ON
OPEN= OFF



CONNECT TO 120V
TRANSFORMER OR
DC/AC INPUT
MATCH FUSE WITH
INPUT CURRENT

PhotoCell Relay
PC ON: COM-NO
PC OFF: COM-NC
For external
accessories control

DC/AC INPUT 80W Max.
28-40VDC/22-28VAC



Onstate Technologies
High Power LED Driver
Current Regulator Board

www.OnstateTech.com
Part: CIR-LDSL
May/11

LAMP POWER OUTPUT
LO: 1.6A
MED: 2.6A
HI: 3.6A
CONSTANT CURRENT